



TUV TL Mini

TUV 11W 4P SE UNP/32

TUV TL Mini lamps are slim double-ended UVC (germicidal) lamps used in residential water and air disinfection units. The small 16 mm diameter of the lamp allows for a small system design and design flexibility. TUV TL Mini lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

Product data

General Information	
Cap-Base	4PINSSINGLEENDED [4 Pins Single Ended]
Useful Life (Nom)	9.000 hour(s)
Light Technical	
Color Code	TUV
Color Designation	- [Not Specified]
Depreciation at Useful Lifetime	15 %

Operating and Electrical	
Power Consumption	11.5 W
Lamp Current (Nom)	0.4 A
Voltage (Nom)	34 V
Voltage (Nom)	34 V
Mechanical and Housing	
Bulb Shape	T16 [T 16mm]

TUV TL Mini

Approval and Application

Mercury (Hg) Content (Nom) 4.4 mg

UV

UV-C Radiation at 100 hr 2.7 W

Product Data

Order product name TUV 11W 4P SE UNP/32

Full product name TUV 11W 4P SE UNP/32

Full product code 871150064382799

Order code 927971204099

Material Nr. (12NC) 927971204099


Numerator - Quantity Per Pack 1

EAN/UPC - Product/Case 8711500643827

Numerator - Packs per outer box 32


EAN/UPC - Case 8711500643841

Dimensional drawing



Product	D (max)	C (max)	A (max)
TUV 11W 4P SE UNP/32	19 mm	251.8 mm	244.1 mm

Photometric data



Spectral Power Distribution Colour - TUV 11W 4P SE UNP/32

