



TUV T5

TUV 36T5 HO 4P SE 32PK

TUV T5 lamps are single- or double-ended UVC (germicidal) lamps used in professional water and air disinfection units. The small 16 mm diameter of the lamp allows for a small system design and design flexibility. TUV T5 lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	4PINSSINGLEENDED [4 Pins Single Ended]
Useful Life (Nom)	9,000 hour(s)
Light Technical	
Color Code	TUV
Color Designation	- [Not Specified]
Depreciation at Useful Lifetime	20 %
Operating and Electrical	
Power Consumption	75 W


Lamp Current (Nom)	0.8 A
Voltage (Nom)	97 V
Voltage (Nom)	97 V
Mechanical and Housing	
Bulb Shape	T16 [T 16mm]
Approval and Application	
Mercury (Hg) Content (Nom)	5.5 mg

TUV T5

UV	
UV-C Radiation at 100 hr	24.4 W
Product Data	
Order product name	TUV 36T5 HO 4P SE UNP/32
Full product name	TUV 36T5 HO 4P SE 32PK
Full product code	871150086970899
Order code	133892

Material Nr. (12NC)	927972104099
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500869708
Numerator - Packs per outer box	32
EAN/UPC - Case	8711500869715

Dimensional drawing



Product	D (max)	C (max)	A (max)
TUV 36T5 HO 4P SE UNP/32	3/4 inch	33-5/8 inch	33-5/16 inch

Photometric data



Spectral Power Distribution Colour - TUV 36T5 HO 4P SE UNP/32

