



# TL Mini Standard Colours

## TL Mini 8W/54-765 FAM/10X25BOX

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	G5 [G5]
Life to 50% Failures (Nom)	5,000 hour(s)
Light Technical	
Color Code	54-765
Luminous Flux	340 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6200 K
Color rendering index (CRI)	75
Operating and Electrical	
Power Consumption	8 W
Lamp Current (Nom)	0.145 A
Voltage (Nom)	127 V


Voltage (Nom)	127 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T5 [16 mm (T5)]
Approval and Application	
Mercury (Hg) Content (Nom)	4.4 mg
Energy Consumption kWh/1000 h	8 kWh
Product Data	
Order product name	TL Mini 8W/54-765 FAM/10X25BOX
Full product name	TL Mini 8W/54-765 FAM/10X25BOX
Full product code	871951428070000

TL Mini Standard Colours

Order code	927974105401
Material Nr. (12NC)	927974105401
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514280700


Numerator - Packs per outer box	250
EAN/UPC - Case	8719514280724

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL Mini 8W/54-765 FAM/ 10X25BOX	16 mm	288.3 mm	295.4 mm	293.0 mm	302.5 mm

Photometric data



Spectral Power Distribution Colour - TL Mini 8W/54-765 FAM/10X25BOX

