



# TL Mini Standard Colours

## TL Mini 8W/54-765 FAM/10X25BOX

This TL Miniature lamp (tube diameter 16 mm) is a lamp with small dimensions, which enables system miniaturization and offers the possibility of operation on low-voltage DC supply. It is ideal for applications where space is limited but where color rendering and efficacy are not the most important factors, such as orientation, signage and emergency lighting.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Voltage (Nom)	
Cap-Base	G5 [G5]	127 V	
Life to 50% Failures (Nom)	5,000 hour(s)	Controls and Dimming	
Light Technical		Dimmable	Yes
Color Code	54-765	Mechanical and Housing	
Luminous Flux	340 lm	Bulb Shape	T5 [16 mm (T5)]
Color Designation	Cool Daylight	Approval and Application	
Correlated Color Temperature (Nom)	6200 K	Mercury (Hg) Content (Nom)	4.4 mg
Color rendering index (CRI)	75	Energy Consumption kWh/1000 h	8 kWh
Operating and Electrical		Product Data	
Power Consumption	8 W	Order product name	TL Mini 8W/54-765 FAM/10X25BOX
Lamp Current (Nom)	0.145 A	Full product name	TL Mini 8W/54-765 FAM/10X25BOX
Voltage (Nom)	127 V		

## TL Mini Standard Colours

Full product code	871951428070000
Order code	927974105401
Material Nr. (12NC)	927974105401
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514280700


Numerator - Packs per outer box	250
EAN/UPC - Case	8719514280724

### Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL Mini 8W/54-765 FAM/ 10X25BOX	16 mm	288.3 mm	295.4 mm	293.0 mm	302.5 mm

### Photometric data



Spectral Power Distribution Colour - TL Mini 8W/54-765 FAM/10X25BOX

