



MASTER TL-D Xtreme



MASTER TL-D Xtreme 18W/840 SLV

This MASTER TL-D Xtreme lamp offers extremely long lifetime. This results in extralow lamp cost over life. It is therefore suitable for places where lamp replacement is expensive, due to high ceilings or disturbance of operations, and applications with long burning cycles, e.g. tunnels, oil rigs, manufacturing lines. It can be operated on existing gear or dedicated HF Xtreme gear.

Warnings and Safety

- To achieve published lifetimes for 100% operation, do not dim below 30%
- When used on electromagnetic gear, it is strongly recommended to apply only Philips S10 or S10E starters (for 18W types S2 or S2E) to achieve the published lifetimes, and to install new starters when relamping.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Color rendering index (CRI)	82	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]			
Flux measurement reference	Sphere	Operating and Electrical		
Life to 50% Failures (Nom)	47,000 hour(s)	Power Consumption	18.0 W	
		Lamp Current (Nom)	0.370 A	
Light Technical				
Color Code	840 [CCT of 4000K]	Controls and Dimming		
Luminous Flux	1,300 lm	Dimmable	Yes	
Color Designation	Cool White (CW)			
Chromaticity Coordinate X (Nom)	0.38	Mechanical and Housing		
Chromaticity Coordinate Y (Nom)	0.38	Bulb Shape	Т8	
Correlated Color Temperature (Nom)	4000 K			
Luminous Efficacy (rated) (Nom)	76 lm/W	Approval and Application		
		Energy Efficiency Class	G	


MASTER TL-D Xtreme

Mercury (Hg) Content (Max)	3 mg		
Mercury (Hg) Content (Nom)	3.0 mg		
Energy Consumption kWh/1000 h	18 kWh		
EPREL Registration Number	423627		
Product Data			
Order product name	MASTER TL-D Xtreme 18W/840 SLV		
Full product name	MASTER TL-D Xtreme 18W/840 SLV		
Full product code	871150054496440		


Order code	927980384014		
Material Nr. (12NC)	927980384014		
Numerator - Quantity Per Pack	1		
EAN/UPC - Product/Case	8711500544964		
Numerator - Packs per outer box	25		
EAN/UPC - Case	8711500544971		

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Xtreme 18W/840	28 mm	589.8 mm	596.9 mm	594.5 mm	604.0 mm
SLV					




Photometric data




Spectral Power Distribution Colour - MASTER TL-D Xtreme 18W/840 SLV


MASTER TL-D Xtreme

Lifetime





Lumen Maintenance Diagram - MASTER TL-D Xtreme 18W/840 SLV



Life Expectancy Diagram - MASTER TL-D Xtreme 18W/840 SLV



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.