



MASTER TL-D Xtra

MASTER TL-D Xtra 18W/865 SLV

Low-pressure mercury discharge lamp with a tubular 26mm envelope

Warnings and Safety

- To achieve published lifetimes for 100% operation, do not dim below 30%
- To achieve published lifetimes for 100% operation, do not dim below 30%
- When used on electromagnetic gear, it is strongly recommended to apply only Philips S10 or S10E starters (for 18W types S2 or S2E) to achieve the published lifetimes, and to install new starters when relamping.
- When used on electromagnetic gear, it is strongly recommended to apply only Philips S10 or S10E starters (for 18W types S2 or S2E) to achieve the published lifetimes, and to install new starters when relamping.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Operating and Electrical	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Power Consumption	17.7 W
Life to 50% Failures (Nom)	36,000 hour(s)	Lamp Current (Nom)	0.370 A
Light Technical		Controls and Dimming	
Color Code	865 [CCT of 6500K]	Dimmable	Yes
Luminous Flux	1,250 lm	Mechanical and Housing	
Color Designation	Cool Daylight	Bulb Shape	T8 [26 mm (T8)]
Correlated Color Temperature (Nom)	6500 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	71 lm/W	Mercury (Hg) Content (Nom)	3.0 mg
Color rendering index (CRI)	>80		

MASTER TL-D Xtra

Energy Consumption kWh/1000 h	22 kWh
Product Data	
Order product name	MASTER TL-D Xtra 18W/865 SLV
Full product name	MASTER TL-D Xtra 18W/865 SLV
Full product code	871150089281240
Order code	927980486514


Material Nr. (12NC)	927980486514
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500892812
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500892829

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Xtra 18W/865 SLV	28 mm	589.8 mm	596.9 mm	594.5 mm	604.0 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL-D Xtra 18W/865 SLV

Lifetime




Life Expectancy Diagram - MASTER TL-D Xtra 18W/865 SLV



Life Expectancy Diagram - MASTER TL-D Xtra 18W/865 SLV

MASTER TL-D Xtra

Lifetime



Life Expectancy Diagram - MASTER TL-D Xtra 18W/865 SLV

Lumen Maintenance Diagram - MASTER TL-D Xtra 18W/865 SLV

