



# MASTER TL-D Super 80

## TL-D 58W/840 1SL/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	15,000 h
Light Technical	
Color Code	840 [CCT of 4000K]
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	89 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	58 W
Lamp Current (Nom)	0.670 A
Voltage (Nom)	111 V
Voltage (Nom)	111 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8
Approval and Application	
Mercury (Hg) Content (Nom)	2.0 mg
Product Data	
Order product name	TL-D 58W/840 1SL/25
Full product name	TL-D 58W/840 1SL/25
Full product code	871829125470600
Local code description	TLD58W840ALTO
Order code	927981584024
Material Nr. (12NC)	927981584024
Local order code	TLD58W840ALTO
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291254706

MASTER TL-D Super 80



Numerator - Packs per outer box	25
EAN/UPC - Case	8718291254713

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 58W/840 1SL/25	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

Lifetime



Life Expectancy Diagram - TL-D 58W/840 1SL/25



Lumen Maintenance Diagram - TL-D 58W/840 1SL/25

Life Expectancy Diagram - TL-D 58W/840 1SL/25

## MASTER TL-D Super 80

