



T5 Standard

F14T5/835/ALTO 40PK

Philips T5 Fluorescent Lamps featuring ALTO® Lamp Technology offer increased energy savings and low toxicity in a slim profile.

Product data

General Information	
Base	G5 [G5]
Life to 50% Failures Preheat (Nom)	24000 h
Features	HE Alto® [High Efficiency Alto]
System Description	High Efficiency
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	99 %
LSF Preheat 8000 h Rated	99 %
LSF Preheat 16000 h Rated	97 %
LSF Preheat 20000 h Rated	84 %
Light Technical	
Color Code	835 [CCT of 3500K]
Initial lumen (Nom)	1350 lm
Luminous Flux (Rated) (Nom)	1200 lm
Color Designation	White (WH)
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	99 lm/W
Correlated Color Temperature (Nom)	3500 K
Luminous Efficacy (rated) (Nom)	86 lm/W
Color Rendering Index (Max)	85
Color Rendering Index (Min)	80
Color Rendering Index (Nom)	82
LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %

LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

Operating and Electrical

Power (Rated) (Nom)	14.0 W
Lamp Current (Nom)	0.165 A

Temperature

Design Temperature (Nom)	35 °C
--------------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Cap-Base Information	Green [Green Cap]
----------------------	--------------------

Approval and Application

Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	1.4 mg

T5 Standard

Product Data


Order product name	14W/835 Min Bipin T5 HE ALTO UNP/40
EAN/UPC - Product	046677230791
Order code	230797
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	40
Material Nr. (12NC)	927990483522
Net Weight (Piece)	54.000 g
ILCOS Code	FDH-14/35/1B-L/P-G5-16

Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050



Dimensional drawing



TL5 HE F14T5/835 HE Alto

Product	D (max)	A (max)	B (max)	B (min)	C (max)
14W/835 Min Bipin T5 HE ALTO UNP/40	17 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm


Photometric data



LDPO_TL5-HE8_835-Spectral power distribution Colour

T5 Standard

Lifetime



LDLE_TL5-HE8_0002-Life expectancy diagram

