



T5 Standard

F21T5/835/ALTO 40PK

Philips T5 Fluorescent Lamps featuring ALTO® Lamp Technology offer increased energy savings and low toxicity in a slim profile.

Product data


G5			
HE Alto® [High Efficiency Alto]			
835 [CCT of 3500K]			
2,100 lm			
White (WH)			
3500 K			
90 lm/W			
82			
20.6 W			
0.165 A			
Yes			

Mechanical and Housing				
Bulb Shape	T5			
Approval and Application				
Mercury (Hg) Content (Nom)	1.4 mg			
Product Data				
Order product name	21W/835 Min Bipin T5 HE ALTO UNP/40			
Full product name	F21T5/835/ALTO 40PK			
Order code	230821			
Material Nr. (12NC)	927990883522			
Numerator - Quantity Per Pack	1			
EAN/UPC - Product/Case	046677230821			
Numerator - Packs per outer box	40			
EAN/UPC - Case	50046677230826			

Datasheet, 2023, April 14 data subject to change


T5 Standard

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
21W/835 Min Bipin T5 HE ALTO	17 mm	849.0 mm	856.1 mm	853.7 mm	863.2 mm
UNP/40					


Photometric data



Spectral Power Distribution Colour - 21W/835 Min Bipin T5 HE ALTO UNP/40

Lifetime






Life Expectancy Diagram - 21W/835 Min Bipin T5 HE ALTO UNP/40

Life Expectancy Diagram - 21W/835 Min Bipin T5 HE ALTO UNP/40

T5 Standard

Lifetime



Lumen Maintenance Diagram - 21W/835 Min Bipin T5 HE ALTO UNP/40



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.