



Eco passport

MASTER TL5 High Efficiency Eco

MASTER TL5 HE Eco 25=28W/840 UNP/40



Energy

- Power (Rated) (Nom) : 25.2 W
- Luminous efficacy (@ max. lumen, rated) (nom.) : 114 lm/W
- Lamp Luminous Efficacy EM (Nom) : 103 lm/W
- Energy efficiency label (EEL) : A+
- Dimmable : yes



Substances

- Mercury (Hg) content (nom.) : 1.4 mg



Lifetime

- Life to 50% failures preheat (nom.) : 25000 h

Our environmental product specifications overview

At Philips, we strive to make the world healthier and more sustainable through innovation. Our sustainability efforts are globally recognised and reflected, e.g. by our continuous leading positions global rankings like the Dow Jones Sustainability Index and the Carbon Disclosure Project. In our eco-design process we focus on Energy, Weight, Recycling, Packaging, Substances and Reliability to view and further improve the environmental performance of our products.

PHILIPS

2019, February 11
data subject to change
Order code : 927990984031