

MASTER TL5 高效环保型

MASTER TL5 HE Eco 25=28W/865 UNP/40

这种高效的 TL5 灯 (荧光灯的直径为 16 毫米)，通过简单的灯换灯的替换可节省大量的能源。在 TL5 HE Eco 生态灯提供了出色的光通维持率和显色。应用领域从办公室、工业区到学校和零售业。

安全提示

- A reduction in energy consumption is only achieved with current-controlled gear.
- The lamps operate perfectly with power-controlled gear, but in that case the light output can be up to 10% higher.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般信息	
底盖	G5 [G5]
功能	na [Not Applicable]
灯技术	
颜色代码	865 [CCT of 6500K]
光通量	2,700 lm
颜色名称	冷日光
相关色温 (标称)	6500 K
光效 (额定)(标称)	96 lm/W
显色指数 (CRI)	82
操作和电气	
功耗	25.2 W


灯具电流 (标称)	0.170 A
控制和调光	
可调光	是
机械和外壳	
灯泡外形	T5 [16 毫米 (T5)]
审批和申请	
汞 (Hg) 含量 (标称)	1.4 mg
能耗 kWh/1000 h	28 kWh
产品数据	
订单产品名称	MASTER TL5 HE Eco 25=28W/865 UNP/40
完整的产品名称	MASTER TL5 HE Eco 25=28W/865 UNP/40

MASTER TL5 高效环保型

完整产品代码	872790090056900
订购代码	927990986531
材料编号 (12NC)	927990986531
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8727900900569


计算器 - 每个外包装箱中的包数	40
EAN/UPC - 案例	8727900900569

二维绘图




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE Eco	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm
25=28W/865 UNP/40					

光度数据




Spectral Power Distribution Colour - MASTER TL5 HE Eco 25=28W/865 UNP/40

寿命




Life Expectancy Diagram - MASTER TL5 HE Eco 25=28W/865 UNP/40



Life Expectancy Diagram - MASTER TL5 HE Eco 25=28W/865 UNP/40

MASTER TL5 高效环保型

寿命



Lumen Maintenance Diagram - MASTER TL5 HE Eco 25=28W/865 UNP/40

