



T5 Energy Advantage

F28T5/835/EA/ALTO 25W 40/1

Philips Energy Advantage T5 lamps featuring ALTO Lamp Technology offer ultimate energy savings without any sacrifice to light levels.

Product data

General Information	
Base	G5 [G5]
Life to 50% Failures Preheat (Nom)	25000 h
Features	HE EA [High Efficiency Energy Advantage]
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	99 %
LSF Preheat 8000 h Rated	99 %
LSF Preheat 16000 h Rated	99 %
LSF Preheat 20000 h Rated	94 %

Light Technical	
Color Code	835 [CCT of 3500K]
Initial lumen (Nom)	2900 lm
Luminous Flux (Rated) (Nom)	2600 lm
Color Designation	White (WH)
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	114 lm/W
Correlated Color Temperature (Nom)	3500 K
Luminous Efficacy (rated) (Nom)	103 lm/W
Color Rendering Index (Max)	85
Color Rendering Index (Min)	80
Color Rendering Index (Nom)	82
LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %

LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

Operating and Electrical	
Power (Rated) (Nom)	25.2 W
Lamp Current (Nom)	0.170 A

Temperature	
Design Temperature (Nom)	35 °C

Controls and Dimming	
Dimmable	Yes

Approval and Application	
Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	1.4 mg


Product Data	
Order product name	F28T5 835 HE EA ALTO 25W
EAN/UPC - Product	046677406318
Order code	406314
Numerator - Quantity Per Pack	1

T5 Energy Advantage

Numerator - Packs per outer box	40
Material Nr. (12NC)	927991383531
Net Weight (Piece)	104.500 g

Warnings and Safety



Dimensional drawing



Product
F28T5 835 HE EA ALTO 25W

TL5 HE Eco F28T5/835 HE EA 25W


Photometric data



Lifetime

T5 Energy Advantage

Lifetime



LDLM_TL5HEECO_0001-Lumen maintenance diagram

