



MASTER TL5 High Output 90 De Luxe

MASTER TL5 HO 90 De Luxe 49W/965 1SL20

This TL5 High Output lamp (tube diameter 16 mm) has excellent color rendering (CRI > 90). This means that colors are presented in a natural way, making them appear rich, deep and enhanced as they do in daylight. Application areas are places where color rendering is key, e.g. the printing industry, libraries, museums, hospitals and shops (jewelry, flowers, clothing, textile, leather, carpets).

Product data

General Information	
Cap-Base	G5 [G5]
Life to 50% Failures Preheat (Nom)	30000 h
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	99 %
LSF Preheat 8000 h Rated	99 %
LSF Preheat 16000 h Rated	97 %
LSF Preheat 20000 h Rated	84 %
Light Technical	
Color Code	965 [CCT of 6500K]
Luminous Flux (Nom)	4200 lm
Luminous Flux (Rated) (Nom)	3725 lm
Color Designation	Cool Daylight
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	85 lm/W
Chromaticity Coordinate X (Nom)	313
Chromaticity Coordinate Y (Nom)	337
Correlated Color Temperature (Nom)	6800 K

Luminous Efficacy (rated) (Nom)	76 lm/W
Color Rendering Index (Nom)	93
LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %
Operating and Electrical	
Power (Nom)	49.2 W
Lamp Current (Nom)	0.255 A
Temperature	
Design Temperature (Nom)	35 °C
Controls and Dimming	
Dimmable	Yes

MASTER TL5 High Output 90 De Luxe

Approval and Application

Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	54 kWh


Product Data

Full product code	871150086972200
Order product name	MASTER TL5 HO 90 De Luxe 49W/965 1SL20

EAN/UPC - Product	8711500869722
Order code	927991596524
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	927991596524
Net Weight (Piece)	127.400 g
ILCOS Code	FDH-49/65/1A-L/P-G5-16/1450

Warnings and Safety



Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 90 De Luxe 49W/965 1SL20	17 mm	1449.0 mm	1456.1 mm	1453.7 mm	1463.2 mm

TL5 HO 49W/965

Photometric data



LDPO_TL5-HO9_965-Spectral power distribution Colour

MASTER TL5 High Output 90 De Luxe

Lifetime



LDLE_TL5-HO9_0001-Life expectancy diagram

