



MASTER TL5 高输出环保型

MASTER TL5 HO Eco 73=80W/840 UNP/40

荧光灯的直径为 16mm

安全提示

- A reduction in energy consumption is only achieved with current-controlled gear.
- The lamps operate perfectly with power-controlled gear, but in that case the light output can be up to 10% higher.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据


一般信息	
底盖	G5 [G5]
功能	na [Not Applicable]
灯技术	
颜色代码	840 [CCT of 4000K]
光通量	7,000 lm
颜色名称	冷白色 (CW)
相关色温 (标称)	4000 K
光效 (额定) (标称)	89 lm/W
显色指数 (CRI)	82
操作和电气	
功耗	73.3 W
灯具电流 (标称)	0.550 A

控制和调光	
可调光	是
机械和外壳	
灯泡外形	T5 [16 毫米 (T5)]
审批和申请	
汞 (Hg) 含量 (标称)	1.2 mg
能耗 kWh/1000 h	80 kWh
产品数据	
订单产品名称	MASTER TL5 HO Eco 73=80W/840 UNP/40
完整的产品名称	MASTER TL5 HO Eco 73=80W/840 UNP/40
完整产品代码	872790082597800
订购代码	927991884031
材料编号 (12NC)	927991884031
计算器 - 每包数量	1

MASTER TL5 高输出环保型


EAN/UPC - 产品/箱	8711500880093
计算器 - 每个外包装箱中的包数	40
EAN/UPC - 案例	8727900825978

二维绘图




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO Eco	17 mm	1,449.0 mm	1,456.1 mm	1,453.7 mm	1,463.2 mm
73=80W/840 UNP/40					

光度数据




Spectral Power Distribution Colour - MASTER TL5 HO Eco 73=80W/840 UNP/40

寿命




Life Expectancy Diagram - MASTER TL5 HO Eco 73=80W/840 UNP/40



Life Expectancy Diagram - MASTER TL5 HO Eco 73=80W/840 UNP/40

MASTER TL5 高输出环保型

寿命



Lumen Maintenance Diagram - MASTER TL5 HO Eco 73=80W/840 UNP/40

