



# T5 High Output Energy Advantage

## F54T5/841/HO/EA/ALTO 49W 40/1

Philips Energy Advantage T5 HO 49W lamps are environmentally-responsible, ultra-slim and have extraordinary light output with increased energy savings.

### Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050


### Product data

General Information	
Cap-Base	G5
Features	HO EA [High Output Energy Advantage]
Light Technical	
Color Code	841 [CCT of 4100K]
Luminous Flux	5,000 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Luminous Efficacy (rated) (Nom)	93 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	48.0 W
Lamp Current (Nom)	0.460 A

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T5
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Product Data	
Order product name	F54T5 841 HO EA ALTO 49W
Full product name	F54T5/841/HO/EA/ALTO 49W 40/1
Order code	220525
Material Nr. (12NC)	927991984031
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677220525
Numerator - Packs per outer box	40
EAN/UPC - Case	50046677220520


# T5 High Output Energy Advantage

## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
F54T5 841 HO EA	11/16 inch	45-1/4 inch	45-9/16 inch	45-7/16 inch	45-13/16 inch
ALTO 49W					

## Photometric data




Spectral Power Distribution Colour - F54T5 841 HO EA ALTO 49W

## Lifetime



Life Expectancy Diagram - F54T5 841 HO EA ALTO 49W



Lumen Maintenance Diagram - F54T5 841 HO EA ALTO 49W

# T5 High Output Energy Advantage

## Lifetime

Life Expectancy Diagram - F54T5 841 HO EA ALTO 49W

