



T5 High Output Energy Advantage

F54T5/850/HO/EA/ALTO 49W 40/1

Philips Energy Advantage T5 HO 49W lamps are environmentally-responsible, ultra-slim and have extraordinary light output with increased energy savings.

Product data

General Information	
Base	G5 [G5]
Life to 50% Failures Preheat (Nom)	30000 h
Features	HO EA [High Output Energy Advantage]
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	99 %
LSF Preheat 8000 h Rated	99 %
LSF Preheat 16000 h Rated	99 %
LSF Preheat 20000 h Rated	94 %
Light Technical	
Color Code	850 [CCT of 5000K]
Initial lumen (Nom)	4800 lm
Luminous Flux (Rated) (Nom)	4275 lm
Color Designation	Daylight
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	98 lm/W
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	89 lm/W
Color Rendering Index (Max)	85
Color Rendering Index (Min)	80

Color Rendering Index (Nom)	82
LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

Operating and Electrical

Power (Rated) (Nom)	48.0 W
Lamp Current (Nom)	0.460 A

Temperature

Design Temperature (Nom)	35 °C
--------------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Approval and Application

Energy Efficiency Label (EEL)	A
-------------------------------	---


T5 High Output Energy Advantage

Mercury (Hg) Content (Nom)	1.4 mg
Product Data	
XUCDM.COPY.Product.Title	F54T5 850 HO EA ALTO 49W
EAN/UPC - Product	046677406493
Order code	406496

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927991985031
Net Weight (Piece)	104.500 g

Warnings and Safety



Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
F54T5 850 HO EA ALTO 49W	17 mm	1149.0 mm	1156.1 mm	1153.7 mm	1163.2 mm

TL5 HO Eco F54T5/850 HO EA 49W

Lifetime



LDLE_TL5ECO_0001-Life expectancy diagram



LDLM_TL5ECO_0001-Lumen maintenance diagram

T5 High Output Energy Advantage

