

# MASTER TL5 High Output 90 De Luxe

## MASTER TL5 HO 90 De Luxe 24W/940 1SL/20

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


### Product data

General Information		Controls and Dimming	
Cap base	G5 [G5]	Dimmable	Yes
Light Technical		Mechanical and Housing	
Colour Code	940 [CCT of 4000K]	Bulb shape	T5 [16 mm (T5)]
Luminous Flux	1,750 lm	Approval and Application	
Colour designation	Cool White (CW)	Mercury (Hg) content (nom.)	1.2 mg
Chromaticity Coordinate X (Nom)	380	Energy consumption kWh/1,000 hours	25 kWh
Chromaticity Coordinate Y (Nom)	380	Product Data	
Correlated Colour Temperature	4000 K	Order product name	MASTER TL5 HO 90 De Luxe 24W/940 1SL20
Luminous efficacy (rated) (nom.)	68 lm/W	Full product name	MASTER TL5 HO 90 De Luxe 24W/940 1SL/20
Colour rendering index (CRI)	91	Full EOC	871150086895400
Operating and Electrical		Order code	86895400
Power Consumption	22.5 W	Material no. (12 NC)	927992094024
Lamp current (nom.)	0.295 A	Local order code	24940
		SAP numerator – quantity per pack	1
		EAN/UPC – Product/Case	8711500868954

# MASTER TL5 High Output 90 De Luxe


Numerator – packs per outer box	20
EAN/UPC - Case	8727900895230

## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 90 De Luxe 24W/940 1SL20	17 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm

## Photometric data




Spectral Power Distribution Colour - MASTER TL5 HO 90 De Luxe 24W/940 1SL20

## Lifetime



Life Expectancy Diagram - MASTER TL5 HO 90 De Luxe 24W/940 1SL20



Life Expectancy Diagram - MASTER TL5 HO 90 De Luxe 24W/940 1SL20

# MASTER TL5 High Output 90 De Luxe

## Lifetime



Lumen Maintenance Diagram - MASTER TL5 HO 90 De Luxe 24W/940  
1SL20

