



# MASTER TL5 High Output 90 De Luxe



## MASTER TL5 HO 90 De Luxe 24W/965 1SL20

This TL5 High Output lamp (tube diameter 16 mm) has excellent color rendering (CRI > 90). This means that colors are presented in a natural way, making them appear rich, deep and enhanced as they do in daylight. Application areas are places where color rendering is key, e.g. the printing industry, libraries, museums, hospitals and shops (jewelry, flowers, clothing, textile, leather, carpets).

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Operating and Electrical	
Cap-Base	G5	Power Consumption	22.8 W
Features	HO Alto® [High Output Alto]	Lamp Current (Nom)	0.295 A
Flux measurement reference	Sphere		
Light Technical		Controls and Dimming	
Color Code	965 [CCT of 6500K]	Dimmable	Yes
Luminous Flux	1,525 lm		
Color Designation	Cool Daylight	Mechanical and Housing	
Chromaticity Coordinate X (Nom)	0.313	Bulb Shape	T5
Chromaticity Coordinate Y (Nom)	0.337		
Correlated Color Temperature (Nom)	6500 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	68 lm/W	Energy Efficiency Class	G
Color rendering index (CRI)	92	Mercury (Hg) Content (Nom)	1.2 mg
		Energy Consumption kWh/1000 h	23 kWh

# MASTER TL5 High Output 90 De Luxe

EPREL Registration Number	423481
<b>Product Data</b>	
Order product name	MASTER TL5 HO 90 De Luxe 24W/965 1SL20
Full product name	MASTER TL5 HO 90 De Luxe 24W/965 1SL20
Full product code	871150026130400
Order code	927992096524


Material Nr. (12NC)	927992096524
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500261304
Numerator - Packs per outer box	20
EAN/UPC - Case	8727900895254

## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 90 De Luxe 24W/965 1SL20	17 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm

## Photometric data




Spectral Power Distribution Colour - MASTER TL5 HO 90 De Luxe 24W/965 1SL20

## Lifetime




Life Expectancy Diagram - MASTER TL5 HO 90 De Luxe 24W/965 1SL20



Life Expectancy Diagram - MASTER TL5 HO 90 De Luxe 24W/965 1SL20

# MASTER TL5 High Output 90 De Luxe

## Lifetime



Lumen Maintenance Diagram - MASTER TL5 HO 90 De Luxe 24W/965  
1SL20

