



MASTER TL5 High Output 90 De Luxe

MASTER TL5 HO 90 De Luxe 24W/965 1SL20

This TL5 High Output lamp (tube diameter 16 mm) has excellent color rendering (CRI > 90). This means that colors are presented in a natural way, making them appear rich, deep and enhanced as they do in daylight. Application areas are places where color rendering is key, e.g. the printing industry, libraries, museums, hospitals and shops (jewelry, flowers, clothing, textile, leather, carpets).

Product data

General Information	
Cap-Base	G5 [G5]
Life to 50% Failures Preheat (Nom)	30000 h
Features	HO Alto® [High Output Alto]
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	99 %
LSF Preheat 8000 h Rated	99 %
LSF Preheat 16000 h Rated	97 %
LSF Preheat 20000 h Rated	84 %

Light Technical	
Color Code	965 [CCT of 6500K]
Luminous Flux (Nom)	1750 lm
Luminous Flux (Rated) (Nom)	1525 lm
Color Designation	Cool Daylight
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	78 lm/W
Chromaticity Coordinate X (Nom)	313
Chromaticity Coordinate Y (Nom)	337

Correlated Color Temperature (Nom)	6800 K
Luminous Efficacy (rated) (Nom)	68 lm/W
Color Rendering Index (Nom)	93
LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

Operating and Electrical	
Power (Nom)	22.5 W
Lamp Current (Nom)	0.295 A

Temperature	
Design Temperature (Nom)	35 °C

MASTER TL5 High Output 90 De Luxe

Controls and Dimming

Dimmable	Yes
----------	-----

Approval and Application

Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	25 kWh


Product Data

Full product code	871150026130400
Order product name	MASTER TL5 HO 90 De Luxe 24W/965 ISL20

EAN/UPC - Product	8711500261304
Order code	927992096524
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	927992096524
Net Weight (Piece)	52.000 g
ILCOS Code	FDH-24/65/1A-L/P-G5-16/550

Warnings and Safety



Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 90 De Luxe 24W/965 ISL20	17 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm

TL5 HO 24W/965

Photometric data



LDPO_TL5-HO9_965-Spectral power distribution Colour

MASTER TL5 High Output 90 De Luxe

Lifetime



LDLE_TL5-HO9_0001-Life expectancy diagram

