

Lighting

PHILIPS

T5 High Output

F24T5/835/HO/ALTO 40PK

Philips T5 HO lamps are environmentally-responsible, ultra-slim and have extraordinary light output and longer life.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050


Product data

General Information			
Cap-Base	G5		
Features	HO Alto® [High Output Alto]		
Light Technical			
Color Code	835 [CCT of 3500K]		
Luminous Flux	1,950 lm		
Color Designation	White (WH)		
Correlated Color Temperature (Nom)	3500 K		
Luminous Efficacy (rated) (Nom)	76 lm/W		
Color rendering index (CRI)	82		
Operating and Electrical			
Power Consumption	22.5 W		
Lamp Current (Nom)	0.295 A		
Controls and Dimming			
Dimmable	Yes		

Т5		
g		
/835 Min Bipin T5 HO ALTO UNP		
5/835/HO/ALTO 40PK		
205		
92183522		
577290207		
46677290202		


T5 High Output

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
24W/835 Min Bipin T5	11/16 inch	21-5/8 inch	21-15/16 inch	21-13/16 inch	22-3/16 inch
HO ALTO UNP					

Photometric data




Spectral Power Distribution Colour - 24W/835 Min Bipin T5 HO ALTO UNP

Lifetime







Lumen Maintenance Diagram - 24W/835 Min Bipin T5 HO ALTO UNP

T5 High Output

Lifetime

Life Expectancy Diagram - 24W/835 Min Bipin T5 HO ALTO UNP



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, September 21 - data subject to change