



T5 Standard

F35T5/830 40PK

Philips T5 Fluorescent Lamps featuring ALTO® Lamp Technology offer increased energy savings and low toxicity in a slim profile.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050


Product data

General Information	
Cap-Base	G5
Features	HE Alto® [High Efficiency Alto]
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	3,650 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	94 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	35.5 W
Lamp Current (Nom)	0.175 A
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T5
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Product Data	
Order product name	F35T5/830 40PK
Full product name	F35T5/830 40PK
Order code	230888
Material Nr. (12NC)	927992783022
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677230883
Numerator - Packs per outer box	40
EAN/UPC - Case	50046677230888


T5 Standard

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
F35T5/830 40PK	11/16 inch	57-1/16 inch	57-3/8 inch	57-1/4 inch	57-5/8 inch

Photometric data




Spectral Power Distribution Colour - F35T5/830 40PK

Lifetime




Life Expectancy Diagram - F35T5/830 40PK



Life Expectancy Diagram - F35T5/830 40PK

T5 Standard

Lifetime



Lumen Maintenance Diagram - F35T5/830 40PK

