



MASTER TL5 High Output 90 De Luxe

MASTER TL5 HO 90 De Luxe 54W/940 1SL20

This TL5 High Output lamp (tube diameter 16 mm) has excellent color rendering (CRI > 90). This means that colors are presented in a natural way, making them appear rich, deep and enhanced as they do in daylight. Application areas are places where color rendering is key, e.g. the printing industry, libraries, museums, hospitals and shops (jewelry, flowers, clothing, textile, leather, carpets).

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Lamp Current (Nom)	
Cap-Base	G5		0.455 A
Light Technical		Controls and Dimming	
Color Code	940 [CCT of 4000K]	Dimmable	Yes
Luminous Flux	4,300 lm	Mechanical and Housing	
Color Designation	Cool White (CW)	Bulb Shape	T5
Chromaticity Coordinate X (Nom)	380	Approval and Application	
Chromaticity Coordinate Y (Nom)	380	Mercury (Hg) Content (Nom)	1.2 mg
Correlated Color Temperature (Nom)	4000 K	Energy Consumption kWh/1000 h	59 kWh
Luminous Efficacy (rated) (Nom)	71 lm/W	Product Data	
Color rendering index (CRI)	91	Order product name	MASTER TL5 HO 90 De Luxe 54W/940 1SL20
Operating and Electrical		Full product name	MASTER TL5 HO 90 De Luxe 54W/940 1SL20
Power Consumption	54.1 W		

MASTER TL5 High Output 90 De Luxe

Full product code	871150086905000
Order code	927993094024
Material Nr. (12NC)	927993094024
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500869050


Numerator - Packs per outer box	20
EAN/UPC - Case	8727900895261

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 90 De Luxe 54W/940 1SL20	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL5 HO 90 De Luxe 54W/940 1SL20

Lifetime




Life Expectancy Diagram - MASTER TL5 HO 90 De Luxe 54W/940 1SL20



Life Expectancy Diagram - MASTER TL5 HO 90 De Luxe 54W/940 1SL20

MASTER TL5 High Output 90 De Luxe

Lifetime



Lumen Maintenance Diagram - MASTER TL5 HO 90 De Luxe 54W/940
1SL20

