



MASTER TL5 High Output 90 De Luxe 高亮度日光燈管

MASTER TL5 HO 90 De Luxe 54W/965 1SL20

This TL5 High Output lamp (tube diameter 16 mm) has excellent color rendering (CRI > 90). This means that colors are presented in a natural way, making them appear rich, deep and enhanced as they do in daylight. Application areas are places where color rendering is key, e.g. the printing industry, libraries, museums, hospitals and shops (jewelry, flowers, clothing, textile, leather, carpets).

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊	
燈座基底	G5 [G5]
功能	HO Alto® [High Output Alto]
通量測量參考	Sphere
照明技術	
色碼	965 [CCT of 6500K]
光通量	3,825 lm
色彩名稱	冷日光色
色度坐標 x (標稱)	0.313
色度坐標 Y (Nom)	0.337
相關色彩溫度 (規範)	6500 K


光效 (額定) (標準)	71 lm/W
演色性指數 (CRI)	92
運轉與電力	
耗電量	54.6 W
燈具電流 (標稱)	0.455 A
控制與調光	
可調光	是

MASTER TL5 High Output 90 De Luxe 高亮度日光燈管

機械與外罩	
燈泡形狀	T5 [16 mm (T5)]
認證與應用	
節能省電等級	G
汞 (Hg) 含量 (標稱)	1.2 mg
能源消耗 kWh/1000 h	55 kWh
EPREL 註冊碼	423485
產品資料	
下訂產品名稱	MASTER TL5 HO 90 De Luxe 54W/965 1SL20


完整產品名稱	MASTER TL5 HO 90 De Luxe 54W/965 1SL20
完整產品代碼	871150086983800
訂單代碼	927993096524
材質 Nr. (12NC)	927993096524
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500869838
分子 - 每一外盒包裝	20
EAN/UPC - 箱	8727900895285

二维绘图



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 90 De Luxe 54W/965 1SL20	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm



光度数据



Spectral Power Distribution Colour - MASTER TL5 HO 90 De Luxe 54W/965 1SL20

MASTER TL5 High Output 90 De Luxe 高亮度日光燈管

壽命



Life Expectancy Diagram - MASTER TL5 HO 90 De Luxe 54W/965 1SL20

Life Expectancy Diagram - MASTER TL5 HO 90 De Luxe 54W/965 1SL20



Lumen Maintenance Diagram - MASTER TL5 HO 90 De Luxe 54W/965 1SL20

