



TL Mini Standard Colours

TL Mini 6W/33-640 FAM/10X25BOX

直径仅 16mm 的低压气体放电灯

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般信息	
底盖	G5 [G5]
光通量测量参考	Sphere
50% 故障条件下的使用寿命 (标称)	10,000 小时
灯技术	
颜色代码	33-640
光通量	260 lm
颜色名称	冷白色 (CW)
色度坐标 X (标称)	0.38
色度坐标 Y (标称)	0.38
相关色温 (标称)	4000 K
光效 (额定)(标称)	43 lm/W
显色指数 (CRI)	59
操作和电气	
功耗	6.0 W
灯具电流 (标称)	0.160 A
电压 (标称)	42 V


电压 (标称)	42 V
控制和调光	
可调光	是
机械和外壳	
灯泡外形	T5 [16 毫米 (T5)]
审批和申请	
能效等级	G
汞 (Hg) 含量 (最高)	2.5 mg
汞 (Hg) 含量 (标称)	4.4 mg
能耗 kWh/1000 h	6 kWh
EPREL 注册号	423488
产品数据	
订单产品名称	TL Mini 6W/33-640 FAM/10X25BOX
完整的产品名称	TL Mini 6W/33-640 FAM/10X25BOX
完整产品代码	871150071583827

TL Mini Standard Colours

订购代码	928000503340
材料编号 (12NC)	928000503340
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500715838


计算器 - 每个外包装箱中的包数	250
EAN/UPC - 案例	8711500715852

二维绘图



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL Mini 6W/33-640 FAM/ 10X25BOX	16 mm	212.1 mm	219.2 mm	216.8 mm	226.3 mm

光度数据



Spectral Power Distribution Colour - TL Mini 6W/33-640 FAM/10X25BOX

