



TUV TL Mini

TUV 6W FAM/10X25BOX

TUV TL Mini lamps are slim double-ended UVC (germicidal) lamps used in residential water and air disinfection units. The small 16 mm diameter of the lamp allows for a small system design and design flexibility. TUV TL Mini lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy.


Product data

General Information		Operating and Electrical	
Cap base	G5 [G5]	Power (Rated) (Nom)	6 W
Remarks	Warnings and safety: A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facility for recycling. Do not use a vacuum cleaner. DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.	Lamp current (nom.)	0.16 A
Main application	Disinfection	Voltage (Nom)	42 V
Useful life (nom.)	9000 h	Mechanical and Housing	
System description	na [-]	Cap base information	na [-]
Light Technical		Approval and Application	
Colour Code	TUV	Mercury (Hg) content (nom.)	4.4 mg
Colour Designation	- [Not Specified]	UV	
Depreciation at Useful Lifetime	20 %	UV-C Radiation	1.7 W
Product Data		Product Data	
Full product code		871150062364527	
Order product name		TUV 6W FAM/10X25BOX	
EAN/UPC – product		8711500623645	
Order code		62364527	
Numerator – quantity per pack		1	
Numerator – packs per outer box		250	

TUV TL Mini

Material no. (12NC)	928000704013
Net weight (piece)	21.000 g

Dimensional drawing



Product	D (max)	B (max)	B (min)	C (max)	A (max)
TUV 6W FAM/10X25BOX	16 mm	219.2 mm	216.8 mm	226.3 mm	212.1 mm

Photometric data

