



TL Mini consumer products

TL Mini 8W/33-640 1PP/10

They come in different wattages and colors with moderate (/33) to good (/827) light quality.

Product data

General Information	
Cap-Base	G5 [G5]
Life To 10% Failures (Nom)	5000 h
Life to 50% Failures (Nom)	10000 h
Life to 50% Failures Preheat (Nom)	10000 h
System Description	-

Light Technical	
Color Code	33-640
Luminous Flux (Nom)	410 lm
Color Designation	Cool White (CW)
Lumen Maintenance 10000 h (Nom)	58 %
Lumen Maintenance 2000 h (Nom)	80 %
Lumen Maintenance 5000 h (Nom)	70 %
Correlated Color Temperature (Nom)	4100 K
Luminous Efficacy (rated) (Nom)	51 lm/W
Color Rendering Index (Nom)	60

Operating and Electrical	
Power (Nom)	7.1 W
Lamp Current (Nom)	0.145 A
Voltage (Nom)	56 V

Controls and Dimming	
Dimmable	Yes


Approval and Application	
Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	4.4 mg
Energy Consumption kWh/1000 h	8 kWh

Product Data	
Full product code	871150062695025
Order product name	TL Mini 8W/33-640 1PP/10
EAN/UPC - Product	8711500626950
Order code	928001003313
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	928001003313
Net Weight (Piece)	27.000 g
ILCOS Code	FD-8/41/2B-E-G5

TL Mini consumer products

Warnings and Safety


Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL Mini 8W/33-640 1PP/10	16 mm	288.3 mm	295.4 mm	293.0 mm	302.5 mm

TL Mini 8W/33-640

Photometric data



LDPB_TL-MINI_33-640-Spectral power distribution B/W



LDPO_TL-MINI_33-640-Spectral power distribution Colour

