



# TL Mini Standard Colours



## TL Mini 8W/54-765 FAM/10X25BOX

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	G5
Flux measurement reference	Sphere
Life to 50% Failures (Nom)	10,000 hour(s)
Light Technical	
Color Code	54-765
Luminous Flux	335 lm
Color Designation	Cool Daylight
Chromaticity Coordinate X (Nom)	0.313
Chromaticity Coordinate Y (Nom)	0.337
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	48 lm/W
Color rendering index (CRI)	72
Operating and Electrical	
Power Consumption	7.1 W
Lamp Current (Nom)	0.145 A
Voltage (Nom)	56 V


Voltage (Nom)	56 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T5
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	2.5 mg
Mercury (Hg) Content (Nom)	4.4 mg
Energy Consumption kWh/1000 h	8 kWh
EPREL Registration Number	423492
Product Data	
Order product name	TL Mini 8W/54-765 FAM/10X25BOX
Full product name	TL Mini 8W/54-765 FAM/10X25BOX
Full product code	871150071628627

TL Mini Standard Colours

Order code	71628627
Material Nr. (12NC)	928001005440
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500716286


Numerator - Packs per outer box	250
EAN/UPC - Case	8711500716309

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL Mini 8W/54-765 FAM/ 10X25BOX	16 mm	288.3 mm	295.4 mm	293.0 mm	302.5 mm

Photometric data



Spectral Power Distribution Colour - TL Mini 8W/54-765 FAM/10X25BOX

