



TUV TL Mini

TUV 8W FAM/10X25BOX

TUV TL Mini lamps are slim double-ended UVC (germicidal) lamps used in residential water and air disinfection units. The small 16 mm diameter of the lamp allows for a small system design and design flexibility. TUV TL Mini lamps offer almost constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy.

Product data


General Information		Operating and Electrical	
Cap-Base	G5 [G5]	Power (Rated) (Nom)	8 W
Remarks	Warnings and Safety: A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner. DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.	Lamp Current (Nom)	0.15 A
Main Application	Disinfection	Voltage (Nom)	56 V
Useful Life (Nom)	11000 h	Mechanical and Housing	
System Description	na [-]	Cap-Base Information	na [-]
Light Technical		Approval and Application	
Color Code	TUV	Mercury (Hg) Content (Nom)	4.4 mg
Color Designation	- [Not Specified]	UV	
Depreciation at Useful Lifetime	15 %	UV-C Radiation at 100 hr	2.4 W
		Product Data	
		Full product code	871150062368327
		Order product name	TUV 8W FAM/10X25BOX
		EAN/UPC - Product	8711500623683
		Order code	928001104013
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	250
		Material Nr. (12NC)	928001104013

TUV TL Mini

Net Weight (Piece) 25.300 g

Warnings and Safety

Dimensional drawing



Product	D (max)	B (max)	B (min)	C (max)	A (max)
TUV 8W FAM/10X25BOX	16 mm	295.4 mm	293 mm	302.5 mm	288.3 mm

Photometric data



TUV

TUV

