



# TL Mini consumer products

## TL Mini 13W/33-640 1PP/10

They come in different wattages and colors with moderate (/33) to good (/827) light quality.

### Product data

General Information	
Cap base	G5 [ G5]
Life to 10% failures (nom.)	4000 h
Life to 50% failures (nom.)	8000 h
Life to 50% failures preheat (nom.)	8000 h
System description	na [-]

### Light Technical

Colour Code	33-640
Lamp Luminous Flux 25°C EL (Nom)	930 lm
Colour Designation	Cool White (CW)
Lumen maintenance 10,000 hours (nom.)	58 %
Lumen maintenance 2,000 hours (nom.)	85 %
Lumen maintenance 5,000 hours (nom.)	70 %
Colour Temperature, horizontal (Nom)	4100 K
Lamp Luminous Efficacy EM (Nom)	71 lm/W
Colour Rendering Index,horiz (Nom)	60

### Operating and Electrical

Power (Rated) (Nom)	13.0 W
Lamp current (nom.)	0.170 A
Voltage (Nom)	90 V

Controls and Dimming	
Dimmable	yes


Approval and Application	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	4.4 mg
Energy Consumption kWh/1000 h	14 kWh

### Product Data

Full product code	871150062698125
Order product name	TL Mini 13W/33-640 1PP/10
EAN/UPC – product	8711500626981
Order code	928001503313
Local Code	TL13W33PP
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	928001503313
Net weight (piece)	40.200 g
ILCOS Code	FD-13/41/2B-E-G5

# TL Mini consumer products


## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL Mini 13W/33-640 1PP/10	16 mm	516.9 mm	524.0 mm	521.6 mm	531.1 mm

### TL Mini 13W/33-640

## Photometric data



### Lightcolour /33-640



### Lightcolour /33-640

