



Blue (/52) TL/TL-D

TL 20W/52 SLV/25

Tubular or compact single-ended low-pressure mercury vapour fluorescent lamps

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	9,000 hour(s)
Useful Life (Nom)	2,000 hour(s)
Light Technical	
Color Code	52
Luminous Flux	318 lm
Chromaticity Coordinate X (Nom)	154
Chromaticity Coordinate Y (Nom)	69
Operating and Electrical	
Power Consumption	19.3 W
Lamp Current (Nom)	0.36 A
Voltage (Nom)	59 V
Voltage (Nom)	59 V
Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Shape	T38
Approval and Application	
Mercury (Hg) Content (Nom)	8.0 mg
Product Data	
Order product name	TL 20W/52 SLV/25
Full product name	TL 20W/52 SLV/25
Full product code	871150064302540
Order code	928003505203
Material Nr. (12NC)	928003505203
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500643025
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500643032


Blue (/52) TL/TL-D

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 20W/52 SLV/25	40.5 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

Photometric data



Spectral Power Distribution Colour - TL 20W/52 SLV/25

