



Blue (/52) TL/TL-D

TL 20W/52 SLV/25

Tubular or compact single-ended low-pressure mercury vapour fluorescent lamps

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


| General Information | |
|---------------------------------|---------------------------------|
| Cap-Base | G13 [Medium Bi-Pin Fluorescent] |
| Life to 50% Failures (Nom) | 9,000 hour(s) |
| Useful Life (Nom) | 2,000 hour(s) |
| Light Technical | |
| Color Code | 52 |
| Luminous Flux | 318 lm |
| Chromaticity Coordinate X (Nom) | 154 |
| Chromaticity Coordinate Y (Nom) | 69 |
| Operating and Electrical | |
| Power Consumption | 19.3 W |
| Lamp Current (Nom) | 0.36 A |
| Voltage (Nom) | 59 V |
| Voltage (Nom) | 59 V |

| Controls and Dimming | |
|---------------------------------|------------------|
| Dimmable | No |
| Mechanical and Housing | |
| Bulb Shape | T38 |
| Approval and Application | |
| Mercury (Hg) Content (Nom) | 8.0 mg |
| Product Data | |
| Order product name | TL 20W/52 SLV/25 |
| Full product name | TL 20W/52 SLV/25 |
| Full product code | 871150064302540 |
| Order code | 928003505203 |
| Material Nr. (12NC) | 928003505203 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500643025 |
| Numerator - Packs per outer box | 25 |

Blue (/52) TL/TL-D


| | |
|----------------|---------------|
| EAN/UPC - Case | 8711500643032 |
|----------------|---------------|

Dimensional drawing



| Product | D (max) | A (max) | B (max) | B (min) | C (max) |
|------------------|---------|----------|----------|----------|---------|
| TL 20W/52 SLV/25 | 40.5 mm | 589.8 mm | 596.9 mm | 594.5 mm | 604 mm |

Photometric data



Spectral Power Distribution Colour - TL 20W/52 SLV/25

