



T12 Standard

F20T12/D-765 25 PK

Low-pressure mercury discharge lamps with a tubular 37 mm envelope

Product data


General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	9,000 hour(s)
Light Technical	
Color Code	54-765
Luminous Flux	975 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6200 K
Color rendering index (CRI)	72
Operating and Electrical	
Power Consumption	19.3 W
Voltage (Nom)	59 V
Voltage (Nom)	59 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T12
Approval and Application	
Mercury (Hg) Content (Nom)	8.0 mg
Product Data	
Order product name	F20T12/D-765 25 PK
Full product name	F20T12/D-765 25 PK
Full product code	871869667308900
Order code	928003505415
Material Nr. (12NC)	928003505415
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696673089
Numerator - Packs per outer box	25
EAN/UPC - Case	8718696673096


T12 Standard

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
F20T12/D-765 25 PK	40.5 mm	589.8 mm	596.9 mm	594.5 mm	604 mm



Photometric data



Spectral Power Distribution Colour - F20T12/D-765 25 PK

