



Eco passport

Flexo Print

TL 100W/10-R UV-A



Energy

- Power (Rated) (Nom) : 100 W



Substances

- Mercury (Hg) content (nom.) : 13.0 mg



Lifetime

- Life to 50% failures (nom.) : 2000 h
- Useful life (nom.) : 1000 h