# Flexo Print

## TL 60W/10-R SLV/25

Tubular low-pressure mercury vapour discharge lamps

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

| General Information | |
|---|---|
| **Cap-Base** | G13 [Medium Bi-Pin Fluorescent] |
| **Life to 50% Failures (Nom)** | 2,000 hour(s) |
| **Useful Life (Nom)** | 1,000 hour(s) |

| Light Technical | |
|---|---|
| **Color Code** | 10-R |
| **Color Designation** | Ultra Violet A |
| **Chromaticity Coordinate X (Nom)** | 222 |
| **Chromaticity Coordinate Y (Nom)** | 210 |
| **UV Depreciation at 1000 h** | 15 % |
| **UV Depreciation at 2000 h** | 30 % |
| **UV Depreciation at 500 h** | 10 % |

| Operating and Electrical | |
|---|---|
| **Power Consumption** | 62 W |
| **Lamp Current (Nom)** | 0.7 A |
| **Voltage (Nom)** | 102 V |
| **Voltage (Nom)** | 102 V |

| Mechanical and Housing | |
|---|---|
| **Bulb Shape** | T38 |

| Approval and Application | |
|---|---|
| **Mercury (Hg) Content (Nom)** | 13.0 mg |

| UV | |
|---|---|
| **UV-A Radiation 100Hr (IEC)** | 15.8 W |

| Product Data | |
|---|---|
| **Order product name** | TL 60W/10-R SLV/25 |
| **Full product name** | TL 60W/10-R SLV/25 |
| **Full product code** | 871150061572540 |
| **Order code** | 928008401003 |
| **Material Nr. (12NC)** | 928008401003 |
| **Numerator - Quantity Per Pack** | 1 |
| **EAN/UPC - Product/Case** | 8711500615725 |
| **Numerator - Packs per outer box** | 25 |
| **EAN/UPC - Case** | 8711500615732 |

# Flexo Print

## Dimensional drawing

| Product | D (max) | A (max) | B (max) | B (min) | C (max) |
|---|---|---|---|---|---|
| TL 60W/10-R SLV/25 | 40.5 mm | 1,199.4 mm | 1,206.5 mm | 1,204.1 mm | 1,213.6 mm |




## Photometric data




Spectral Power Distribution Colour - TL 60W/10-R SLV/25