



# Actinic BL TL-D(K) Secura

## Actinic BL TL-D TL 8W/10 Secura 1FM/10X25CC

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL-D(K) Secura lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. In addition, they have a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice.

### Product data

General Information	
Cap base	G5 [ G5]
Life to 50% failures (nom.)	10000 h
Useful life (max.)	3000 h

Light Technical	
Colour code	10
Depreciation at 500 Hours	17 %
Depreciation at 1000 Hours	25 %
Depreciation at 500 Hours	35 %

Operating and Electrical	
Power (Rated) (Nom)	7.1 W
Lamp current (nom.)	0.145 A
Voltage (Nom)	56 V

Approval and Application	
Mercury (Hg) content (nom.)	4.4 mg

UV	
UV-B/UV-A (IEC)	0.2 %
UV-A radiation 100 hours (IEC)	1.6 W


Product Data	
Full product code	871829168010900
Order product name	Actinic BL TL-D TL 8W/10 Secura 1FM/10X25CC
EAN/UPC – product	8718291680109
Order code	68010900
Local Code	TL8W10
Numerator – quantity per pack	1
Numerator – packs per outer box	250
Material no. (12NC)	928011001029
Net weight (piece)	25.300 g

# Actinic BL TL-D(K) Secura

## Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D TL 8W/10	16 mm	288.3 mm	295.4 mm	293.0 mm	302.5 mm
Secura 1FM/10X25CC					

## TL 8W/10 Secura

## Photometric data



## Lightcolour /10



## Lightcolour /10

