



# Actinic BL TL(-K) / TL-D(-K)

## Actinic BL TL 40W/10 SLV/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data


General Information		UV Depreciation at 2000 h		Operating and Electrical	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	UV Depreciation at 2000 h	20 %	Power Consumption	39 W
Life to 50% Failures (Nom)	9,000 hour(s)	UV Depreciation at 5000 h	40 %	Lamp Current (Nom)	0.43 A
Useful Life (Nom)	5,000 hour(s)			Voltage (Nom)	101 V
				Voltage (Nom)	101 V
Light Technical					
Color Code	10				
Color Designation	Actinic				
Chromaticity Coordinate X (Nom)	220				
Chromaticity Coordinate Y (Nom)	205				

# Actinic BL TL(-K) / TL-D(-K)

Mechanical and Housing	
Bulb Shape	T12
Approval and Application	
Mercury (Hg) Content (Nom)	13.0 mg
UV	
UV-A Radiation 0Hr (IEC)	12.4 W
UV-A Radiation 100Hr (IEC)	10.0 W
Product Data	
Order product name	Actinic BL TL 40W/10 SLV/25


Full product name	Actinic BL TL 40W/10 SLV/25
Full product code	871150026026000
Order code	391532
Material Nr. (12NC)	928011301020
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500260260
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500260277

## Dimensional drawing



Product	D (max)	A (max)	B	C (max)
Actinic BL TL 40W/10 SLV/25	1-1/2 inch	47-3/16 inch	47-1/2 inch	47-3/4 inch

## Photometric data



Spectral Power Distribution Colour - Actinic BL TL 40W/10 SLV/25

## Actinic BL TL(-K) / TL-D(-K)

