



TL Rapid Start Standard Colours

TL 40W/54-765 RSYL 1SL/25

The TL RS (Rapid Start) lamp (tube diameter 38 mm) has an external silicon coating. It is suitable for situations where high humidity requires fast and stable ignition but color rendering is not important. Rapid Start lamps can be ignited without a starter.


Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	12,000 hour(s)
Light Technical	
Color Code	54-765
Luminous Flux	2,700 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6200 K
Luminous Efficacy (rated) (Nom)	68.5 lm/W
Color rendering index (CRI)	75
Operating and Electrical	
Power Consumption	39.0 W
Lamp Current (Nom)	0.440 A
Voltage (Nom)	103 V
Voltage (Nom)	103 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T12
Approval and Application	
Mercury (Hg) Content (Nom)	8.0 mg
Product Data	
Order product name	TL 40W/54-765 RSYL 1SL/25
Full product name	TL 40W/54-765 RSYL 1SL/25
Full product code	871829172550300
Order code	928012305430
Material Nr. (12NC)	928012305430
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291725503
Numerator - Packs per outer box	25
EAN/UPC - Case	8718291725510


TL Rapid Start Standard Colours

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 40W/54-765 RSYL 1SL/25	28.0 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

Photometric data



Spectral Power Distribution Colour - TL 40W/54-765 RSYL 1SL/25

