



# Actinic BL TL(-K)/TL-D(-K)

## ACTINIC BL TL-DK - 30W/10 1SL

Tubular low-pressure mercury vapour fluorescent lamps

### Product data


General Information	
Cap base	G13 [ Medium Bi-Pin Fluorescent]
Main application	Insect traps
Life to 50% failures (nom.)	2000 h
Useful life (nom.)	2000 h
Light Technical	
Colour Code	10
Colour Designation	Actinic
Chromaticity coordinate X (nom.)	225
Chromaticity coordinate Y (nom.)	230
Depreciation at 500 Hours	15 %
Depreciation at 1000 Hours	25 %
Depreciation at 500 Hours	40 %
Operating and Electrical	
Power (Rated) (Nom)	30 W
Lamp current (nom.)	0.805 A
Voltage (Nom)	45 V

Approval and Application	
Mercury (Hg) content (nom.)	8.0 mg
UV	
UV-B/UV-A (IEC)	02 %
UV-A radiation 100 hours (IEC)	6.6 W
Product Data	
Full product code	871150089346840
Order product name	ACTINIC BL TL-DK - 30W/10 1SL
EAN/UPC – product	8711500893468
Order code	928019501029
Local Code	TLDK30W/10
Numerator – quantity per pack	1
Numerator – packs per outer box	25
Material no. (12NC)	928019501029
Net weight (piece)	59.600 g

### Warnings and Safety

# Actinic BL TL(-K)/TL-D(-K)

## Dimensional drawing




### Product


ACTINIC BL TL-DK - 30W/10 1SL

TL-DK 30W/10

## Photometric data



Lightcolour /10



Lightcolour /10

