



MASTER Actinic BL TL-D

MASTER Actinic BL TL-D 15W/10 1SL/25

The Philips MASTER Actinic BL TL-D(-K) family is an ideal choice for insect traps. These lamps have the perfect spectrum for attracting insects. Also, they have virtually no UV-B output, and so are perfectly safe. Furthermore, they have the special "MASTER" coating to improve the efficiency, initial UV-A output and maintenance of the lamp. What's more, with the lowest mercury content in the industry and being 100% lead-free, combined with their high efficiency, these lamps represent the best choice for the environment. Optionally, for extra safety you can apply a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Chromaticity Coordinate Y (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	UV Depreciation at 2000 h	7 %
Life to 50% Failures (Nom)	13,000 hour(s)	UV Depreciation at 5000 h	14 %
Useful Life (Nom)	12,000 hour(s)	UV Depreciation at 8000 h	18 %
Light Technical		Operating and Electrical	
Color Code	10	Power Consumption	15.9 W
Color Designation	Actinic	Lamp Current (Nom)	0.335 A
Chromaticity Coordinate X (Nom)	225	Voltage (Nom)	55 V

MASTER Actinic BL TL-D

Voltage (Nom)	55 V
Mechanical and Housing	
Bulb Shape	T26
Approval and Application	
Mercury (Hg) Content (Nom)	3.0 mg
UV	
UV-A Radiation 100Hr (IEC)	4.0 W
Product Data	
Order product name	MASTER Actinic BL TL-D 15W/10 1SL/25


Full product name	MASTER Actinic BL TL-D 15W/10 1SL/25
Full product code	872790092696500
Order code	928022601003
Material Nr. (12NC)	928022601003
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900926965
Numerator - Packs per outer box	25
EAN/UPC - Case	8727900926972

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER Actinic BL TL-D 15W/10 1SL/25	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm

Photometric data



Spectral Power Distribution Colour - MASTER Actinic BL TL-D 15W/10 1SL/25

MASTER Actinic BL TL-D

