



MASTER Actinic BL TL-D Secura

MASTER Actinic BL TL-D 15W/10 Secura

The Philips MASTER Actinic BL TL-D Secura family combines multiple benefits in one lamp. These lamps have the perfect spectrum for attracting insects. Also, they have virtually no UV-B output, and so are perfectly safe. Furthermore, they have the special "MASTER" coating to improve the efficiency, initial UV-A output and maintenance of the lamp. And finally, they have a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements. What's more, with the lowest mercury content in the industry and being 100% lead-free, combined with their high efficiency, these lamps represent the best choice for the environment.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	13,000 hour(s)
Useful Life (Nom)	12,000 hour(s)
Light Technical	
Color Code	10
Color Designation	Actinic
Chromaticity Coordinate X (Nom)	225
Chromaticity Coordinate Y (Nom)	215


UV Depreciation at 2000 h	7 %
UV Depreciation at 5000 h	14 %
UV Depreciation at 8000 h	18 %
Operating and Electrical	
Power Consumption	15.5 W
Lamp Current (Nom)	0.335 A
Voltage (Nom)	55 V
Voltage (Nom)	55 V

MASTER Actinic BL TL-D Secura

Mechanical and Housing	
Bulb Shape	T26
Approval and Application	
Mercury (Hg) Content (Nom)	3.0 mg
UV	
UV-A Radiation 100Hr (IEC)	3.15 W
Product Data	
Order product name	MASTER Actinic BL TL-D 15W/10 Secura


Full product name	MASTER Actinic BL TL-D 15W/10 Secura
Full product code	871829119608200
Order code	928022701003
Material Nr. (12NC)	928022701003
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291196082
Numerator - Packs per outer box	25
EAN/UPC - Case	8718291196099

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER Actinic BL TL-D 15W/10 Secura	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm

Photometric data



Spectral Power Distribution Colour - MASTER Actinic BL TL-D 15W/10 Secura

MASTER Actinic BL TL-D Secura

