

# Preheat T8

## F15T8/D 25PK

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

### Product data

| General Information        |                                  |
|----------------------------|----------------------------------|
| Base                       | G13 [ Medium Bi-Pin Fluorescent] |
| Life To 10% Failures (Nom) | 10000 h                          |
| Life to 50% Failures (Nom) | 13000 h                          |
| Features                   | ALTO® (ALTO)                     |

| Light Technical                    |               |
|------------------------------------|---------------|
| Color Code                         | 54-765        |
| Initial lumen (Nom)                | 725 lm        |
| Color Designation                  | Cool Daylight |
| Lumen Maintenance 10000 h (Nom)    | 75 %          |
| Lumen Maintenance 2000 h (Nom)     | 90 %          |
| Lumen Maintenance 5000 h (Nom)     | 80 %          |
| Correlated Color Temperature (Nom) | 6200 K        |
| Color Rendering Index (Nom)        | 75            |

| Operating and Electrical |         |
|--------------------------|---------|
| Power (Rated) (Nom)      | 15.5 W  |
| Lamp Current (Nom)       | 0.335 A |
| Voltage (Nom)            | 55 V    |

| Controls and Dimming |     |
|----------------------|-----|
| Dimmable             | Yes |

| Mechanical and Housing |                    |
|------------------------|--------------------|
| Cap-Base Information   | Green [ Green Cap] |

| Approval and Application   |        |
|----------------------------|--------|
| Mercury (Hg) Content (Nom) | 2.0 mg |


  

| Product Data                    |              |
|---------------------------------|--------------|
| Order product name              | F15T8/D 25PK |
| EAN/UPC - Product               | 046677378233 |
| Order code                      | 407205       |
| Numerator - Quantity Per Pack   | 1            |
| Numerator - Packs per outer box | 25           |
| Material Nr. (12NC)             | 928022805425 |
| Net Weight (Piece)              | 59.600 g     |

### Warnings and Safety

# Preheat T8

## Dimensional drawing




TL-D F15T8 Cool Daylight/GC ALTO


### Product

F15T8/D 25PK

## Photometric data




LDPB\_TL-DSTD\_54-765-Spectral power distribution B/W




LDPO\_TL-DSTD\_54-765-Spectral power distribution Colour

## Lifetime




LDLE\_TL-DSTD\_0001-Life expectancy diagram



LDLE\_TL-DSTD\_0002-Life expectancy diagram

## Preheat T8

### Lifetime



LDLM\_TL-DSTD\_0001-Lumen maintenance diagram

