



Retail Sales T8

F15T8 BRIGHT WHITE/18 ALTO 6PK

Energy Savings, extra long life, extra low mercury T8 lamps offer high energy savings, superior lumen output, and long life in an environmentally responsible lamp.

Product data

| General Information | |
|----------------------------|----------------------------------|
| Base | G13 [Medium Bi-Pin Fluorescent] |
| Life To 10% Failures (Nom) | 10000 h |
| Life to 50% Failures (Nom) | 13000 h |
| Features | ALTO® (ALTO) |

| Light Technical | |
|------------------------------------|---------------------|
| Color Code | 830 [CCT of 3000K] |
| Initial lumen (Nom) | 990 lm |
| Color Designation | Soft White |
| Lumen Maintenance 2000 h (Nom) | 93 % |
| Lumen Maintenance 5000 h (Nom) | 88 % |
| Correlated Color Temperature (Nom) | 3000 K |
| Color Rendering Index (Nom) | 83 |

| Operating and Electrical | |
|--------------------------|---------|
| Power (Rated) (Nom) | 15.5 W |
| Lamp Current (Nom) | 0.335 A |
| Voltage (Nom) | 55 V |

| Controls and Dimming | |
|----------------------|-----|
| Dimmable | Yes |

| Mechanical and Housing | |
|------------------------|--------------------|
| Cap-Base Information | Green [Green Cap] |

| Approval and Application | |
|-------------------------------|--------|
| Energy Efficiency Label (EEL) | A |
| Mercury (Hg) Content (Nom) | 2.0 mg |

| Product Data | |
|---------------------------------|--------------------------------|
| Order product name | F15T8 BRIGHT WHITE/18 ALTO SL6 |
| EAN/UPC - Product | 046677392123 |
| Order code | 392126 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 6 |
| Material Nr. (12NC) | 928022883028 |
| Net Weight (Piece) | 59.600 g |

Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Retail Sales T8


Dimensional drawing





TL-D F15T8 Soft White/GC ALTO

| Product | D (max) | A (max) | B (max) | B (min) | C (max) |
|---------------------|---------|----------|----------|----------|----------|
| F15T8 SOFT WHITE/18 | 28 mm | 437.4 mm | 444.5 mm | 442.1 mm | 451.6 mm |
| ALTO SL6 | | | | | |

Lifetime



LDLE_TL-DSTD_0001-Life expectancy diagram



LDLM_TL-DSTD_0001-Lumen maintenance diagram

