



Retail Sales T8

F15T8/NATURAL SUNSHINE SL6

Energy Savings, extra long life, extra low mercury. T8 lamps offer high energy savings, superior lumen output, and long life in an environmentally responsible lamp.


Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	950 [CCT of 5000K]
Luminous Flux	750 lm
Color Designation	Natural Sunshine (NS)
Correlated Color Temperature (Nom)	5000 K
Color rendering index (CRI)	97
Operating and Electrical	
Power Consumption	15.5 W
Lamp Current (Nom)	0.335 A
Voltage (Nom)	55 V
Voltage (Nom)	55 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T8 [26 mm (T8)]
Approval and Application	
Mercury (Hg) Content (Nom)	2.0 mg
Product Data	
Order product name	F15T8/NATURAL SUNSHINE SL6
Full product name	F15T8/NATURAL SUNSHINE SL6
Order code	928022895028
Material Nr. (12NC)	928022895028
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677392291
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677392296



Retail Sales T8

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
F15T8/NATURAL SUNSHINE SL6	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm

Lifetime



Life Expectancy Diagram - F15T8/NATURAL SUNSHINE SL6

Life Expectancy Diagram - F15T8/NATURAL SUNSHINE SL6



Lumen Maintenance Diagram - F15T8/NATURAL SUNSHINE SL6

