



# TL-D Standard Colours

## TL-D 10W/54-765 1SL/50

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

### Product data

General Information	
Cap base	G13 [ Medium Bi-Pin Fluorescent]
Life to 50% failures (nom.)	5000 h

Light Technical	
Colour Code	54-765
Lamp Luminous Flux 25°C EL (Nom)	390 lm
Colour Designation	Cool Daylight
Lumen maintenance 2,000 hours (nom.)	85 %
Lumen maintenance 5,000 hours (nom.)	80 %
Colour Temperature, horizontal (Nom)	6200 K
Colour Rendering Index,horiz (Nom)	75

Operating and Electrical	
Power (Rated) (Nom)	10.0 W
Lamp current (nom.)	0.230 A
Voltage (Nom)	46 V

Controls and Dimming	
Dimmable	yes

Approval and Application	
Energy efficiency label (EEL)	B
Mercury (Hg) content (nom.)	8.0 mg

Product Data	
Full product code	871150064130465
Order product name	TL-D 10W/54-765 1SL/50
EAN/UPC – product	8711500641304
Order code	928024005436
Numerator – quantity per pack	1
Numerator – packs per outer box	50
Material no. (12NC)	928024005436
Net weight (piece)	0.045 kg
ILCOS Code	FD-10/62/2A-E-G13

### Warnings and Safety

# TL-D Standard Colours

## Dimensional drawing




TL-D 10W/54-765


### Product

TL-D 10W/54-765 1SL/50

## Photometric data





Lightcolour /54-765



Lightcolour /54-765


## Lifetime



LDLE\_TL-DSTD\_0001-Life expectancy diagram

## TL-D Standard Colours

### Lifetime



LDLM\_TL-DSTD\_0001-Lumen maintenance diagram

