



# TL-D Standard Colours

## TL-D 10W/54-765 1SL/50

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

### Product data

General Information		Approval and Application	
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]	Energy Efficiency Label (EEL)	B
Life to 50% Failures (Nom)	5000 h	Mercury (Hg) Content (Nom)	8.0 mg
Light Technical		Product Data	
Color Code	54-765	Full product code	871150064130465
Luminous Flux (Nom)	390 lm	Order product name	TL-D 10W/54-765 1SL/50
Color Designation	Cool Daylight	EAN/UPC - Product	8711500641304
Lumen Maintenance 2000 h (Nom)	85 %	Order code	928024005436
Lumen Maintenance 5000 h (Nom)	80 %	Numerator - Quantity Per Pack	1
Correlated Color Temperature (Nom)	6200 K	Numerator - Packs per outer box	50
Color Rendering Index (Nom)	75	Material Nr. (12NC)	928024005436
Operating and Electrical		Net Weight (Piece)	0.045 kg
Power (Nom)	10.0 W	ILCOS Code	FD-10/62/2A-E-G13
Lamp Current (Nom)	0.230 A		
Voltage (Nom)	46 V		
Controls and Dimming			
Dimmable	Yes		

### Warnings and Safety

# TL-D Standard Colours

## Dimensional drawing




TL-D 10W/54-765


### Product

TL-D 10W/54-765 1SL/50

## Photometric data




LDPB\_TL-DSTD\_54-765-Spectral power distribution B/W




LDPO\_TL-DSTD\_54-765-Spectral power distribution Colour

## Lifetime



LDLE\_TL-DSTD\_0001-Life expectancy diagram



LDLE\_TL-DSTD\_0002-Life expectancy diagram

## TL-D Standard Colours

### Lifetime



LDLM\_TL-DSTD\_0001-Lumen maintenance diagram

