



# Actinic BL TL-D(K) Secura

### Actinic BL TL-D 15W/10 Secura 1SL/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL-D(K) Secura lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. In addition, they have a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice.

#### **Warnings and Safety**

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

#### **Product data**

General Information					
Cap-Base	G13 [Medium Bi-Pin Fluorescent]				
Life to 50% Failures (Nom)	8,000 hour(s)				
Useful Life (Nom)	9,000 hour(s)				
Light Technical					
Color Code	10				
Color Designation	Actinic				
Chromaticity Coordinate X (Nom)	222				
Chromaticity Coordinate Y (Nom)	210				
UV Depreciation at 2000 h	25 %				

UV Depreciation at 5000 h	40 %	
Operating and Electrical		
Power Consumption	15 W	
Lamp Current (Nom)	0.335 A	
Voltage (Nom)	55 V	
Voltage (Nom)	55 V	
Mechanical and Housing		
Bulb Shape	T26	


Datasheet, 2023, April 16 data subject to change

## Actinic BL TL-D(K) Secura

Approval and Application					
Mercury (Hg) Content (Nom)	5				
UV					
UV-A Radiation 100Hr (IEC)	3.15 W				
Product Data					
Order product name	Actinic BL TL-D 15W/10 Secura 1SL/25				
Full product name	Actinic BL TL-D 15W/10 Secura 1SL/25				


Full product code	871150089858640		
Order code	89858640		
Material Nr. (12NC)	928024701029		
Numerator - Quantity Per Pack	1		
EAN/UPC - Product/Case	8711500898586		
Numerator - Packs per outer box	25		
EAN/UPC - Case	8711500898593		

#### Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D 15W/10 Secura	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm
1SL/25					

#### Photometric data



Spectral Power Distribution Colour - Actinic BL TL-D 15W/10 Secura 1SL/25



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.