



# Actinic BL TL-D(K) Secura

## Actinic BL TL-D 15W/10 Secura 1SL/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL-D(K) Secura lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. In addition, they have a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	8,000 hour(s)
Useful Life (Nom)	9,000 hour(s)
Light Technical	
Color Code	10
Color Designation	Actinic
Chromaticity Coordinate X (Nom)	222


Chromaticity Coordinate Y (Nom)	210
UV Depreciation at 2000 h	25 %
UV Depreciation at 5000 h	40 %
Operating and Electrical	
Power Consumption	15 W
Lamp Current (Nom)	0.335 A
Voltage (Nom)	55 V

Actinic BL TL-D(K) Secura

Voltage (Nom)	55 V
Mechanical and Housing	
Bulb Shape	T26 [T 26mm]
Approval and Application	
Mercury (Hg) Content (Nom)	5
UV	
UV-A Radiation 100Hr (IEC)	3.15 W
Product Data	
Order product name	Actinic BL TL-D 15W/10 Secura 1SL/25


Full product name	Actinic BL TL-D 15W/10 Secura 1SL/25
Full product code	871150089858640
Order code	928024701029
Material Nr. (12NC)	928024701029
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500898586
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500898593

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D 15W/10 Secura 1SL/25	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm

Photometric data



Spectral Power Distribution Colour - Actinic BL TL-D 15W/10 Secura 1SL/25

## Actinic BL TL-D(K) Secura

