



Actinic BL TL-D(K) Secura

Actinic BL TL-D TL-D 15W/10 Secura 1SL/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL-D(K) Secura lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. In addition, they have a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice.

Product data

| General Information | | Voltage (Nom) | |
|----------------------------------|----------------------------------|---------------------------------|-------------------------------------------|
| Cap base | G13 [Medium Bi-Pin Fluorescent] | 51 V | |
| Main application | Insect traps | Approval and Application | |
| Life to 50% failures (nom.) | 11000 h | Mercury (Hg) content (nom.) | 5.5 mg |
| Useful life (nom.) | 9000 h | UV | |
| Light Technical | | UV-B/UV-A (IEC) | 0.2 % |
| Colour Code | 10 | UV-A radiation 100 hours (IEC) | 3.15 W |
| Colour Designation | Actinic | Product Data | |
| Chromaticity coordinate X (nom.) | 222 | Full product code | 871150089858640 |
| Chromaticity coordinate Y (nom.) | 210 | Order product name | Actinic BL TL-D TL-D 15W/10 Secura 1SL/25 |
| Depreciation at 500 Hours | 25 % | EAN/UPC – product | 8711500898586 |
| Depreciation at 500 Hours | 40 % | Order code | 89858640 |
| Operating and Electrical | | Numerator – quantity per pack | 1 |
| Power (Rated) (Nom) | 15 W | Numerator – packs per outer box | 25 |
| Lamp current (nom.) | 0.335 A | Material no. (12NC) | 928024701029 |

Actinic BL TL-D(K) Secura

| | |
|--------------------|----------|
| Net weight (piece) | 61.000 g |
|--------------------|----------|



Warnings and Safety

Dimensional drawing

| Product | D (max) | A (max) | B (max) | B (min) | C (max) |
|----------------------------------------------|---------|----------|----------|----------|----------|
| Actinic BL TL-D TL-D 15W/10 Secura 1SL/25 | 28 mm | 437.4 mm | 444.5 mm | 442.1 mm | 451.6 mm |

TL-D 15W/10 SECU

Photometric data



Lightcolour /10

Lightcolour /10

