



Actinic BL TL-D(K) Secura

Actinic BL TL-D 15W/10 Secura 1SL/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL-D(K) Secura lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. In addition, they have a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		UV Depreciation at 5000 h	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		40 %
Life to 50% Failures (Nom)	8,000 hour(s)	Operating and Electrical	
Useful Life (Nom)	9,000 hour(s)	Power Consumption	15 W
		Lamp Current (Nom)	0.335 A
Light Technical		Voltage (Nom)	55 V
Color Code	10	Voltage (Nom)	55 V
Color Designation	Actinic	Mechanical and Housing	
Chromaticity Coordinate X (Nom)	222	Bulb Shape	T26
Chromaticity Coordinate Y (Nom)	210		
UV Depreciation at 2000 h	25 %		

Actinic BL TL-D(K) Secura

Approval and Application

Mercury (Hg) Content (Nom) 5

UV

UV-A Radiation 100Hr (IEC) 3.15 W

Product Data

Order product name Actinic BL TL-D 15W/10 Secura 1SL/25

Full product name Actinic BL TL-D 15W/10 Secura 1SL/25

Full product code 871150089858640

Order code 928024701029

Material Nr. (12NC) 928024701029


Numerator - Quantity Per Pack 1

EAN/UPC - Product/Case 8711500898586

Numerator - Packs per outer box 25


EAN/UPC - Case 8711500898593

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D 15W/10 Secura 1SL/25	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm

Photometric data



Spectral Power Distribution Colour - Actinic BL TL-D 15W/10 Secura 1SL/25

