



# TL-D Standard Colours

## TL-D 15W/33-640 1SL/9

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	33-640
Luminous Flux	830 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	63
Operating and Electrical	
Power Consumption	15.0 W
Lamp Current (Nom)	0.310 A
Voltage (Nom)	51 V
Voltage (Nom)	51 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8
Approval and Application	
Mercury (Hg) Content (Nom)	8.0 mg
Product Data	
Order product name	TL-D 15W/33-640 1SL/9
Full product name	TL-D 15W/33-640 1SL/9
Full product code	871150070277700
Order code	928024803347
Material Nr. (12NC)	928024803347
Local order code	TLD15W33
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500702777
Numerator - Packs per outer box	9

TL-D Standard Colours


EAN/UPC - Case	8711500287441
----------------	---------------

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 15W/33-640 1SL/9	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm

Photometric data




Spectral Power Distribution Colour - TL-D 15W/33-640 1SL/9

Lifetime



Life Expectancy Diagram - TL-D 15W/33-640 1SL/9



Life Expectancy Diagram - TL-D 15W/33-640 1SL/9

TL-D Standard Colours

Lifetime



Lumen Maintenance Diagram - TL-D 15W/33-640 1SL/9

